

# OMRON Battery-operated / AC Adapter-operated (or rechargeable) Blood Pressure Monitor Information for Accompanying Documents in the Scope of IEC 60601-1:2005+A1:2012+A2:2020, IEC 60601-1-2:2014+A1:2020 and IEC 60601-1-11:2015+A1:2020

## Important information regarding Electromagnetic Compatibility (EMC)

This blood pressure monitor manufactured by OMRON HEALTHCARE Co., Ltd. conforms to IEC 60601-1:2005+A1:2012+A2:2020, IEC 60601-1-2:2014+A1:2020 and IEC 60601-1-11:2015+A1:2020 Electromagnetic Compatibility (EMC) standard. Nevertheless, special precautions need to be observed:

- The use of accessories and cables other than those specified or provided by OMRON could result in increased electromagnetic emission or decreased electromagnetic immunity of the monitor and result in improper operation.
- During measurement, the use of the monitor adjacent to or stacked with other device should be avoided because it could result in improper operation. In case such use is necessary, the monitor and other device should be observed to verify that they are operating normally.
- During measurement, portable RF communications device (including peripherals such as antenna cables and external antennas) should be used no closer than 12 inches (30 cm) to any part of the monitor, including cables specified by OMRON. Otherwise, degradation of the performance of the monitor could result.
- In environments that do not meet the electromagnetic immunity standards, the monitors performance (accuracy of pressure:  $\pm 3$  mmHg) may deteriorate and correct measurement results may not be obtained.

**Table 1 - EMISSION Limits and Compliance**

Phenomenon	EMISSION Limits	Compliance
Conducted and radiated RF EMISSIONS	CISPR 11	Group1, Class B
Voltage fluctuations and flicker	See IEC 61000-3-3	Complies
Harmonic Emissions IEC 61000-3-2	Not Applicable	Not Applicable

**Table 2 - IMMUNITY TEST LEVELS**

Phenomenon	Basic EMC standard	IMMUNITY TEST LEVELS
Electrostatic discharge	IEC 61000-4-2	$\pm 8$ kV contact $\pm 2$ kV, $\pm 4$ kV, $\pm 8$ kV, $\pm 15$ kV air for enclosure port
Radiated RF electromagnetic fields	IEC 61000-4-3	10 V/m 80 MHz to 2.7 GHz 80 % AM at 1 kHz for enclosure port
Proximity fields from RF wireless communications equipment	IEC 61000-4-3	See table 3
Electrical fast transients / bursts	IEC 61000-4-4	$\pm 2$ kV for Input a.c. power port 100 kHz repetition frequency
Surges Line-to-line	IEC 61000-4-5	$\pm 0.5$ kV, $\pm 1$ kV for Input a.c. power port
Conducted disturbances induced by RF fields	IEC 61000-4-6	3 Vrms 150 kHz to 80 MHz 6 Vrms in ISM and amateur radio bands between 150 kHz and 80 MHz 80 % AM at 1 kHz for Input a.c. power port
Rated power frequency magnetic fields	IEC 61000-4-8	30 A/m 50 Hz and 60 Hz for enclosure port
Voltage dips	IEC 61000-4-11	0 % $U_T$ ; 0.5 cycle At 0°, 45°, 90°, 135°, 180°, 225°, 270° and 315° for Input a.c. power port 0 % $U_T$ ; 1 cycle and 70 % $U_T$ ; 25/30 cycles single phase: at 0° for Input a.c. power port
Voltage interruptions	IEC 61000-4-11	0 % $U_T$ ; 250/300 cycle for Input a.c. power port
Proximity magnetic fields	IEC 61000-4-39	See table 4

NOTE:  $U_T$  is the A.C. mains voltage prior to application of the test level.

**Table 3 - Test specifications for ENCLOSURE PORT IMMUNITY to RF wireless communications device**

Test frequency (MHz)	Band (MHz)	Service	Modulation	Maximum power (W)	Distance (m)	IMMUNITY TEST LEVEL (V/m)
385	380 to 390	TETRA 400	Pulse modulation 18 Hz	1.8	0.3	27
450	430 to 470	GMRS 460, FRS 460	FM $\pm 5$ kHz deviation 1 kHz sine	2	0.3	28
656	614 to 698	5G Band n71	Pulse modulation 217 Hz	0.2	0.3	9
710	704 to 787	LTE Band 13, 17	Pulse modulation 217 Hz	0.2	0.3	9
745						
780						
810	800 to 960	GSM 800/900, TETRA 800, iDEN 820, CDMA 850, LTE Band 5 WPT 920MHz	Pulse modulation 18 Hz	2	0.3	28
870						
930						
1720	1700 to 1990	GSM 1800; CDMA 1900; GSM 1900; DECT; LTE Band 1, 3, 4, 25; UMTS	Pulse modulation 217 Hz	2	0.3	28
1845						
1970						
2450	2400 to 2570	Bluetooth, WLAN, 802.11 b/g/n, RFID 2450, LTE Band 7 WPT 2.4GHz	Pulse modulation 217 Hz	2	0.3	28
2593	2496 to 2690	5G Band n41	Pulse modulation 217 Hz	0.2	0.3	9
3625	3550 to 3700	5G Band n77	Pulse modulation 217 Hz	0.2	0.3	9
3950	3700 to 4200	5G Band n77	Pulse modulation 217 Hz	0.2	0.3	9
5240	5100 to 5800	WLAN 802.11a	Pulse modulation 217 Hz	0.2	0.3	9
5500						
5785						

**Table 4 - Test specifications for ENCLOSURE PORT IMMUNITY to proximity magnetic fields**

Test frequency	Service	Modulation	IMMUNITY TEST LEVEL (A/m)
30 kHz	IH (Induction Heating)	CW	8
134.2 kHz	RFID	Pulse modulation 2.1 kHz	65
13.56 MHz	WPT (Qi)	Pulse modulation 50 kHz	7.5

EMC tests have included the AC adapter.